





### ISO 4401-02-01-0-05



Ports P, A, B, T max Ø4.5 mm (0.18 in)

# Typical circuit with pilot operated check valve




### **Technical Features**

- Pilot to open check valve, poppet-type with subplate mounting interface acc. to ISO 4401, DIN 24340 (CETOP 02)
- > Sandwich plate design for use in vertical stacking assemblies
- Sharp-edged steel seats for dirt-tolerant performance
- > Leak-free closing, suitable for fast cycling with long life
- High flow capacity
- In the standard version, the valve housing is phosphated and steel parts are zinc-coated for 240 h protection acc. to ISO 9227

### **Functional Description**

The valve allows flow to pass from port A(B)1 to A(B)2 while normally under load inhibiting flow from A(B)2 to A(B)1. When pressure is applied at the pilot port, the valve is opened and flow passes from port 2 to 1. The valve has a 3:1 pilot ratio, meaning that at least one third of the load pressure must be applied to open the valve. The check valve is spring closed to secure the holding position in static conditions and without load.




### **Technical Data**

Valve size		04 (D02)
Max. flow	l/min (GPM)	20 (5.3)
Max. operating pressure	bar (PSI)	320 (4640)
Cracking pressure	bar (PSI)	1 (14.5)
Fluid temperature range (NBR)	°C (°F)	-30 +100 (-22 +212)
Fluid temperature range (FPM)	°C (°F)	-20 +120 (-4 +248)
Pilot ratio		3:1
Mass	kg (lbs)	0.7 (1.54)

	Datasheet	Туре
General information	GI_0060	Products and operating conditions
Mounting interface / tolerances	SMT_0019	Size 04
Spare parts	SP_8010	

### **Characteristics** measured at $v = 32 \text{ mm}^2\text{/s}$ (156 SUS)


### Pressure drop related to flow rate




	Flow direction	
1	A1→A2 (B1→B2)	
2	A2→A1 (B2→B1)	

Page 1 www.argo-hytos.com








# **Functional symbols**


# P1 A1 B1 T1

VJR1-04/MA






## VJR1-04/MC



- ① valve side
  - subplate or manifold side

Notes: The orientation of the symbol on the name plate corresponds with the valve function.

# Ordering Code



www.argo-hytos.com Page 2